

AUSDIGISERITT

DESCRIPTION

Transparent adhesive for the Laser and Solvent DIGISERI system for white fabrics. Use on prints from **any** printer and **any** solvent-ecosolvent plotter.

TECHNICAL DATA

AUSDIGISERITT is a **water based** mixture of polymers

EQUIPMENT

Screen printing equipment

SUITABLE FOR

Cotton and other natural or synthetic **white fabrics**



FEATURES

AUSDIGISERITT is a **transparent adhesive for white fabrics** formulated for screen printing. Recommended: **55T to 21T** mesh frames. Use with transfer papers: **AUCFCDIGISERI1** for **Laser** and **AUCPSDIGISERI** for **Solvent-ecosolvent**.

INSTRUCTIONS

Ready for use. If necessary dilute to 5% with water. Stir well before use.

1

Place the screen accurately on the transfer paper **AUCFCDIGISERI1** (Laser) or **AUCPSDIGISERI** (Solvent). **Print the transparent adhesive AUSDIGISERITT** and **dry in heater** (max 70 °C) for 40"-50" or **air dry** for 2 hours.

2

Place the printed side of the transfer paper on the fabric.

3

Procede with the heatpress:

Air press: 180 °C for 20" - pressure 5atm

4

Manual press: 180 °C for 20" - high pressure

Cold peel off transfer paper

5

For better washing resistance press again with adhesive-proof tissue paper (**AU CFC VELIN**) for 10".

6

WARNINGS

Printed fabrics can be machine washed at **40 °C**, 48 hours after application. Iron inside out or use protection. For more info contact your dealer.

Store in a cool and dry place.

Keep away from direct sun light.

Correct storage ensures 2 years shelf life.

STORAGE

The instructions on this sheet are merely indicative and contain details concerning tests carried out in our laboratories with our equipment. Do your own testing. The manufacturer will replace defective material but is not responsible for any damage resulting from incorrect use.

* **Available sizes:** 0.5 Kg - 1 Kg - 5 Kg

SHOCKLINE
about your transfer paper

T. +39 (0)875 751194 - F. +39 (0)875 751329
info@shockline.it - skype shock.line
www.shockline.it

code